



6110401EN3-715: One Light Mini-Pendant



Dimensions:

Diameter:	4"	Overall Height:	53 1/2"
Height:	7 1/4"	Wire:	120" (color/Brown)
Weight:	3 lbs.	Chain:	3"
		Mounting Proc.:	Dual Mount
		Connection:	Mounted To Box

Bulbs:

1 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.

Collection: Sfera

UPC #:785652046834

Finish: Autumn Bronze (715)

Material List:

1 Body - Steel - Undefined
3 12" Stem - Steel - Undefined
1 6" Stem - Steel - Undefined

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990P6110401-SFR)
Trilingual (English, Spanish, and French) (ADD_CHAIN VAULT)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Mercury	1	G560106-640			6 1/2	3 1/2	3 1/2			3 1/2

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 1/4			5		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted		A19	Medium	9.5	9.5	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	6110401BLE-715	1	785652046834	13.5	8.2	7.5	0.48	3.8	125	Yes
NJ Pallet		180		48	40	72	80	684		No