



40G25
40 Watt; G25; Clear; 3000 Average Rated Hours; 360 Lumens;
Medium Base; 120 Volts

Features

- Decorative incandescent
- Long Life
- Brass Base



S3448

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3448	045923034480	40	G25	Medium	E26	40G25	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	4 3/8"	3.13"	CC-9	360	3000	72/6	Box



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

