



Powering Business Worldwide

pe.eaton.com

Eaton Series G molded case circuit breaker accessories and terminals

TA1000NB1

UPC:786679612286

Dimensions:

- **Height:** 3.4 IN
- **Length:** 2.6 IN
- **Width:** 2.6 IN

Weight:.85 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Standard Cu/Al pressure terminals
- **Amperage Rating:** 1000A
- **Wire Size:** (3) #3/0 AWG-400 kcmil
- **Used With:** N-frame
- **Series:** Series G

Supporting documents:

- [Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)
- [Application of Tap Rules to Molded Case Breaker Terminals](#)
- [Motor protection circuit breakers product aid](#)
- [High performance operating handles for Series G circuit breakers product aid](#)
- [Current limiting molded case circuit breaker module product aid](#)
- [Current limiting molded case circuit breaker module for series G, JG and CL](#)
- [Comprehensive circuit protection for control](#)



[panel applications](#)

- [Power metering and monitoring with Modbus RTU product aid](#)
- [Multi-wire lugs product aid](#)
- [Molded case circuit breakers providing higher levels of selective coordination product aid](#)
- [Plug-in adapters for molded case circuit breakers product aid](#)
- [Circuit breaker motor operators product aid](#)
- [StrandAble terminals product aid](#)
- [Series G MCCB quick selector](#)
- [Molded case circuit breakers](#)
- [Eaton's Volume 4-Circuit Protection](#)
- [Breaker service centers](#)
- [MOEM MCCB product selection guide](#)
- [NG and ND-Frame molded case circuit breakers](#)
- [Eaton Specification Sheet - TA1000NB1](#)

Certifications: No Data

Product compliance:

- [Contact Manufacturer](#)