



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



Deluxe A-Frame Mobile Caddy

Deluxe A-Frame Mobile Caddy

Cat No: 9510

UPC No: 783310012146

Description

- Holds up to twenty for (24) spools of #12 AWG wire or sixteen (16) spools of #10 AWG wire
- Folds for easy storage
- 10 IN (254 mm) diameter pneumatic tires for jobsite portability
- Pinless design eliminates loose parts
- Eight (8) solid steel 1/2 IN (12.7 mm) spindles included

Specifications

- Capacity : Maximum Total Spool Weight: 400.000 LB (181.000 KG), Maximum Spool Diameter: 7.500 IN (190.000 MM), Maximum Spool Width: 18.000 IN (457.000 MM)
- Replacement Part : 01207 Spindle (9505/9510)
- Size : 48.000 IN (1219.000 MM) Height X 28-1/4 IN (718.000 MM) Width
- Type : Deluxe A Frame, Mobile
- Weight : 47.000 LB (21.000 KG)