

## MNR1615BN

Manor Flush Mount  
Brushed Nickel  
Manor

# QUOIZEL®



### DIMENSIONS

Dimensions: 15" W x 5.5" H x 15" D

Overall Height: --

Backplate Dimensions: --

Canopy Dimensions: 15.00"W x 15.00"D

Chain/Downrod Length: --

HCWO: --

Weight: 4.60 lbs

Dimensional Weight: 11.00 lbs.

### DETAILS

Material: GLASS

Glass/Shade Description: White Alabaster  
Shade

Shade 2 Description: --

Shade 3 Description: --

### LAMPING

Light Source: Incandescent

Bulb Included: No

Bulb Type: Medium Base

Bulb Quantity: 3

Watts per Bulb: 75

Diffusers: --

### PHOTOMETRICS

LED

Lumens: --

Color Rendering: --

Color Temperature: --

### ELECTRICAL

Dimmable: --

Voltage: 120v W/No Transformer

Wire Length: 0.5'

### INSTALLATION

ADA: --

Location Rating: Damp

Install Position: --

Sloped Ceiling Compatible: Yes

We reserve the right to revise the design of components of any product due to parts availability or change in our Listed Mark standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product DESIGN that is the SOLE and EXCLUSIVE PROPERTY of Quoizel Lighting Inc. Compliance with U.S. COPYRIGHT and PATENT requirements, notification is hereby presented in this form that this literature, or this product depicts, is NOT to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Quoizel Inc. 03/31/2013