



U5136-O-200S-FMG
200A RL MTR DB PED
784572276116

Brand Name: Milbank
Type: Ringless Meter Socket
Special Features: Florida Meter Group
Application: Mobile Home Power
Standard: UL Listed
Voltage Rating: Up to 240 Volts Alternating Current
Amperage Rating: 200 Continuous Ampere
Phase: 1 Phase
Frequency Rating: 60 Hertz
Size: 10.25H x 9.688W x 80H
Number Of Cutouts: 1
Cutout Size: 200 Ampere Main Breaker
Cable Entry: Underground
Terminal: Double Mechanical
Insulation: Glass Polyester
Mounting: Pedestal Mount
Enclosure: G90 Galvanized Steel with Power Coat Finish
Jaw Quantity: 4 Terminal
Bypass Type: Horn Bypass
Number of Metered Positions: Single Power Head
Equipment Ground: Ground Bar
Hub Opening: Plain Top
Line Side Wire Range: 6 AWG - 350 kcmil
Load Side Wire Range: 1/0 AWG - 300 kcmil



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.



U5136-O-200S-FMG
200A RL MTR DB PED
784572276116

Number Branch 6
Circuits:
Number Receptacles: 0

Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.