



Job Name:

Job Type:

Comments:

Quantity:

3313-02: Five-Light Brass Chandelier



Collection: Traditional

Five Light Polished Brass Chandelier w/Optional Shades.

Five light chandelier with polished brass finish.

Material Content Subject to Change and Should not be Publicized

UPC #:785652331329

Finish: Polished Brass (02)

Dimensions:

Diameter: 20 1/4"

Height: 14 3/4"

Overall Height: 52 1/2"

Wire: 144" (color/Gold)

Chain: 36"

Mounting Proc.: Center Lock-Up

Bulb Appearance: Clear

Bulbs:

5 - Candelabra Torpedo 60w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps

Material List:

1 Body - Steel - Polished Brass

5 Arms - Steel - Polished Brass

5 Candle Cover - Polycarbonate - White

1 Chain - Steel - Polished Brass

Safety Listing:

UL Listed for Dry Locations

cUL Listed for Dry Locations

Instruction Sheets:

English (HC-113)

French (F-004)

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1	5 1/8		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	3313-02	1	785652331329	13.5	13.25	8	0.828	5.4	125	Yes
NJ Pallet		70		48	40	72	80	378		No
NV Pallet		90		48	40	71	78.889	486		No



Job Name:

Job Type:

Comments:

Quantity:

3313-962: Five-Light Chandelier



Collection: Traditional

Five Light Chandelier in Brushed Nickel Finish

Material Content Subject to Change and Should not be Publicized

UPC #:785652331398

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 20 1/4"

Height: 14 3/4"

Overall Height: 52 1/2"

Wire: 144" (color/Clear)

Chain: 36"

Mounting Proc.: Center Lock-Up

Bulb Appearance: Clear

Bulbs:

5 - Candelabra Torpedo 60w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps

Material List:

- 1 Body - Steel - Brushed Nickel
- 5 Arms - Steel - Brushed Nickel
- 5 Candle Cover - Polycarbonate - White
- 1 Chain - Steel - Brushed Nickel

Safety Listing:

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

Instruction Sheets:

- English (HC-113)
- French (F-004)

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1	5 1/8		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	3313-962	1	785652331398	14.25	14.25	8	0.94	5.5	150	Yes
NJ Pallet		75		48	40	71	78.889	412.5		No
NV Pallet		90		48	40	71	78.889	486		No