



Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs - Type BQ, 2-Pole, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. 2-Pole Common-Trip circuit breaker type BQ. Rated 120/240V (020A) (AIR 10 kA). Special features: Load side lugs are included.

Number of poles	2
Suitability for operation	Electrical Distribution
Electricity	
Continuous current rated value	20 A
Model	
product brandname	SIEMENS
Type of electrical connection	BOLT-ON
Mechanical Design	
Depth [in]	4 in
Design of the product	BQ
Height [in]	2 in
Width [in]	3 in
General product approval	
Standard	UL 489
last modified:	08/20/2017