

NIMBUS® PBT INS BLK SPL/OFFSET



- Broad wire range: 750kcmil-14
- UL listed and CSA certified for 600 volts, 90°C
- Dual rated for copper or aluminum conductor
- Cold temperature rated to -45°C
- High dielectric strength plastisol is chemical resistant
- Black cover is UV rated
- Removable port & screw plugs
- Prefilled with De-ox
- Per NEC Article 310-16 Allowable Ampacities are as follows: # 4 - 95 Amps, 1/0 - 170 Amps, 3/0 - 225 Amps, 250 - 290 Amps, 350 - 350 Amps, 500 - 430 Amps, 750 - 535 Amps
- UL File E6207

Item ID	Figure Number	Number of Ports	Conductor Range	Length	Width	Height	Hex Size	Standard Package Quantity	NAED/UPC Number
PBT-500	1	2	500 kcmil-4 AWG	5.7810	1.3750	3.0030	3/8	2	0783669077063