

Outdoor Miscellaneous Collection

Outdoor Wall 1Lt

1148WH (White)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____



Ordering Information

Product ID	1148WH
Finish	White
Available Finishes	BK, TZ, WH
Collection	Outdoor Miscellaneous Collection

Dimensions

Extension	5.50"
Height from center of Wall opening	2.25"
Base Backplate	4.50 DIA
Weight	0.50 LBS

Specifications

Material	Steel
Glass Description	Clear

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Wet
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	1
Max or Nominal Watt	75W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	7.50"
Width	4.50"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	18-25W		

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.