



# Advantage T8

## F32T8/ADV841 ALTO 30PK

Philips Advantage T8 lamps are an energy-efficient solution and offer high lumen output.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	36000 h
Life 12-Hr Instant Start [Hrs]	30000 h
Life 3-Hr Program Start [Hrs]	30000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

Light Technical	
Color Code	Advantage 841 [ CCT of 4100K (842)]
Luminous Flux (Nom)	3100 lm
Color Designation	Advantage 841
Design Mean Lumens	3000 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	32 W

### Warnings and Safety

- In order to ensure the integrity of the coating, it is strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48


Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	24 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F32T8/ADV841 ALTO 30PK
EAN/UPC - Product	046677280857
Order code	927869784203
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927869784203
Net Weight (Piece)	0.001 kg

Advantage T8

Dimensional drawing

Product
F32T8/ADV841 ALTO 30PK



F32T8/842 48 ALTO ES

