



Siemens Low Voltage Residential Specialty Load Centers: Murray.  
 Load Centers Features: UL Application: Residential V. Rating:  
 120/240V A. Rating: 200A Phase: 1PH Load Regulation: 200A  
 Wiring Conf: 3w Bus Rating: 200A Interrupt Rating: 22000AIC Circuit  
 Breaker Type: MB No. Of Spaces: 40S Size (H x W x D):  
 5x15.88x40.5 Mounting: Combination Enclosure: Indoor Type 1

Configuration of the busbars	200A
Mounting type	Combination
Phase number	1
Suitability for operation	Residential
<b>Electricity</b>	
Ampacity	200 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V
<b>Switching capacity</b>	
Switching capacity current acc. to EN 60898 rated value	22000 A
<b>Model</b>	
product brandname	Murray
Product sub brand name	Load Centers
Special product feature	UL
<b>Mechanical Design</b>	
Depth [in]	40.5 in

Height [in]	15.88 in
Number of width units for installation width	40
Size of the circuit-breaker	MB
Width [in]	5 in
<b>last modified:</b>	06/05/2017