



BURNDY Catalog Number
UPC Number
Description
Status

YA34A7N131T12E
 7818102813766
 ALLUG-500KCM-1/2-NARTNG
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.88
Bolt Hole Size (in)	0.52
Thickness	0.35
B Length (in)	1.64
Pad Width (in)	1.31
Strip Length	1-11/16

General

Product Description	Cu & Al Compression terminal, 1 Hole/W/insp W, 4/0 AWG-500kcmil, 600V-35Kv, 1/2" stud, Pink, 300 Index, Narrow tongue terminal
---------------------	--

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG-500 kcmil

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Pink
Plated (Yes or No)	N
Index Number	300
Product Material	Aluminum

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175