



RC7CTC MULTI-SERVICE ASSEMBLED POKE-THRU DEVICE

RC7CTC | [Wiremold](#)

FEATURES & BENEFITS

Prewired 20A duplex receptacle can be wired as standard duplex or isolated ground. Flanges available painted in gray (GY), black (BK), ivory (VY). Flanges also available in plated brushed brass (BS) and brushed aluminum (AL). Slide covers match the painted flange colors, gray, black, ivory. Aluminum and brass flanges shipped with black slide cover. Brass flange also available with nonmetallic brass colored slide holder (AB). Aluminum flange also available with nonmetallic aluminum color slide holder (AA). Includes Wiremold Open System unloaded inserts. NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters. RC7 Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

SPECIFICATIONS

GENERAL INFO

Available Colors:

RC7CTCGY - Gray

RC7CTCBK - Black

RC7CTCAL - Brushed Aluminum

RC7CTCBS - Brass

RC7CTCVY - Ivory

RC7CTCAB - All Brass Colored

RC7CTCAA - All Aluminum Colored

Product Series: RC7

Type: Multi-Service

Component Type: Cover Assemblies

DIMENSIONS

Hole Size: 3"

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



