

KTC SERIES - 2 Lamp Troffer Kit Prismatic T5 or T8

2X2 or 2X4 Kit

reflect-a-light®

✓ Made in USA ✓ Universal Fit ✓ High Speed Production ✓ Quick Install

Application

- Retail
- Offices
- Schools

Benefits

- Instant On - Re-Strike
- Up To 90% Energy Savings
- EPACT and Utility Rebates

Features

- Toolless Ballast Access
- BAA Qualified
- ETL Certified

Photometry

- 2 Lamp 2X4 T8-KTC-02B04-EA
- Efficiency: 92.1%
- 0-DEG: 1.2
- 90-DEG: 1.0
- Report Number: 17684

Design

- Made in USA
- Reflector Dimensions: 45.50" x 20.63" x 1.75"
- Snap-in reflector design
- Brackets are universal with multiple mounting options
- Sockets snap-in & twist-lock
- Innovative wire way-less feature

Existing Fixture	Input Watts	System Lumens
4 Lamp F40 T12	192	9120
2 Lamp F40 T12	96	4560
4 Lamp F34 T12	144	7930
4 Lamp F34 T12	72	3960
Retrofit Options	Input Watts	System Lumens
2 Lamp F32 T8 Normal	57	5192
2 Lamp F32 T8 Low	51	4602
2 Lamp F32 T8 High	75	6961
2 Lamp F28 T8 HE/Normal	49	4654
2 Lamp F28 T8 HE/Low	43	4119
2 Lamp F28 T8 HE/High	66	6152

*Lamp/ballast information provided from GE based on Proline ballast and F32T8/SPX41/ECO lamps.
High efficient system based on GE Ultra Max ballast and F28T8/SPX41/ECO lamps



Fixture Ordering Guide Example

KTC-02B04-EA-FLS

Series	Lamps	Wattage	Length	Material	Sockets
KTC	02 - 2 Lamp	B - T8 C - T5	02 - 2' 04 - 4'	EA - 95% Enhanced Aluminum SA - 86% Specular Aluminum WA - 91% White Aluminum	FLS - Shunted FLN - Non Shunted

Option Ordering Guide

See Standard Option Guide



Industry Leader in
Customization + Lead Times
for Over 25 Years

VIDALIA, GA
1-800-537-1629

US Energy Sciences
reflecting technology™