



S5878

MS400/ED28 /PS /U /4K
400 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5878

Item Number	UPC		Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code	
S5878	045923058783		400	ED28	Mogul	E39	M155/E	MS400/ED28 /PS /U /4K	
Finish	MOL In Inches	MOD In Inches	Average Rated Hours		Initial Lumens		Kelvin Temp	Color	Pulse Start
Clear	8.31"	3.56"	20000		44000		4200	Cool White	Yes
Pack	Package Type		CRI	Burning Position		Hg Content		RoHS Compliant	
12	Box		65	Universal		47.5 mg		Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

