



Item #: F594-ORB	UPC Code: 706411039904
Product Family Name:	Finish: Oil Rubbed Bronze
Category: Exterior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents	
Notes:	



Image File Name:
F594-ORB--
1377184850.jpg



MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
ABS Construction		No	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	3	14 degrees	22.53
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
11.00	7.50	8	172X20MM

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	60		116		178
Amps:	0.28		0.46		0.50
Watts:	14.000		33.500		60.500
CFM:	2760.00		5074.13		6565.40
CFM/Watts:	197.14		151.47		108.52



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
		WCS212
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS212	

LAMPING

No. of Bulbs:	Light Type:			
1	Mini-Can Halogen			
Max Bulb Wattage:	Socket:			
100	E11			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
Yes	Yes			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes				

GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
RM191	1
Width:	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
13.000	12.880	23.750	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
24.948	2.301	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



Wet Location

Yes



Title 17

Yes



UL Listed

Yes