



Powering Business Worldwide

pe.eaton.com

## C25 Definite Purpose Control Contactor

**C25GNF290A**

**UPC:** 782114100165

**Dimensions:** 4.41 IN \* 3.86 IN \* 5 IN (L \* W \* H)

**Notes:** No Data

**Warranty:** Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Accessories:** Mounting plate
- **Auxiliary Contact:** Quick connect
- **Coil Voltage:** 110-120 Vac, 50/60 Hz
- **Frame Size:** 90A, two- and three-pole
- **Model:** Open
- **Number Of Poles:** Two-pole
- **Options:** Individual pkg.
- **Series:** F1
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25GNF2 2D PDF](#)
- [C25GNF2 3D Model Xchange](#)
- [C25GNF2 2D Drawing Xchange](#)
- [C25GNF2 AutoCAD 2D Footprint](#)
- [C25GNF2 AutoCAD 2D Footprint \(mm\)](#)
- [C25GNF2 3D Inventor](#)
- [Eaton Specification Sheet - C25GNF290A](#)

**Certifications:** No Data

**Product compliance:** No Data



