

TradeMaster Decorator Combination Switch, Light Almond

TM8111LACC



Decorator Combo, 3 Single Pole Switches,
Light Almond

features & benefits

- Impact-resistant face and body.
- Fully rounded back body protects wires from being damaged by sharp edges.
- Clear identification of circuits.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Full wraparound metal strap with lock-in tabs.
- Patented split circuit tab -- easily accessible, and can be reinstalled without a tool.
- Unique "Up/Down" switches match the look and feel of standard Decorator switches.
- Largest breadth of 15 amp offering.
- All screws are tri-drive.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

specifications

General Info

Product Series: TradeMaster
Type: Combination
Number Of Poles: 1
Style: Decorator

Listing Agencies/Third Party Information

cULus: Yes
UL Listing No: 20
UL Standard: Yes
UN SPS C: 39121704

Dimensions

Depth U S: 1.59"
Height U S: 3.81"
Width U S: 1.29

Technical Information

Amps: 15 Amp
Volts: 120VAC

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No