



U1256-X-KK-K3-BLG  
200A 4T RL 6P CTR WY  
784572241732

**Brand Name:** Milbank  
**Type:** Ringless Meter Socket  
**Application:** Meter Socket  
**Standard:** UL Listed  
**Voltage Rating:** 300 Volts Alternating Current  
**Amperage Rating:** 200 Continuous Ampere  
**Phase:** 1 Phase  
**Frequency Rating:** 60 Hertz  
**Size:** 5.125H x 62.875W x 18H  
**Number Of Cutouts:** 0  
**Cutout Size:** No Main Breaker  
**Cable Entry:** Overhead and Underground, Center Wireway  
**Terminal:** Single Mechanical Line Side and Lay in Load Side  
**Insulation:** Glass Polyester  
**Mounting:** Surface Mount  
**Enclosure:** Type 3R, G90 Galvanized Steel with Powder Coat Finish  
**Jaw Quantity:** 4 Terminal  
**Bypass Type:** Horn Bypass  
**Number of Metered Positions:** 6 Positions  
**Equipment Ground:** Ground Lug  
**Hub Opening:** Large Closing Plate  
**Line Side Wire Range:** 4 AWG - 600 kcmil or Two 1/0 AWG - 250 kcmil  
**Load Side Wire Range:** 6 AWG - 350 kcmil



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*



U1256-X-KK-K3-BLG  
200A 4T RL 6P CTR WY  
784572241732

Barrel Lock Provision: 7/8 Inch Knockout and Angle Bracket  
for Barrel Lock Provision

Number Receptacles: 0

*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*