



Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshows | Support

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Vinyl Electrical Tapes](#) > 3M™ Temflex™ Vinyl Electrical Tape 1700P, MSHA Printed, 1 1/2 in x 66 ft

[Find An Account Rep](#) [Where To Buy \(Find A Distributor\)](#) [Contact Us](#)

3M™ Temflex™ Vinyl Electrical Tape 1700P, MSHA Printed, 1 1/2 in x 66 ft

3M ID 80610737894 UPC# 00054007507505 Part Number 1700P-PRINTED-1-1/2X66FT



3M™ Temflex™ Vinyl Electrical Tape 1700 is a good quality, economical general purpose vinyl insulating tape. It has excellent resistance to abrasion, moisture, alkalies, acid, copper corrosion and varying weather conditions. It is a polyvinyl chloride (PVC) tape that is flame-retardant and conformable. MSHA Printed.

- 1 1/2 in x 66 ft, Black, MSHA Printed
- General purpose vinyl insulating tape
- Resistance to abrasion, moisture, alkalies, acid, copper corrosion and varying weather conditions
- Polyvinyl chloride (PVC) tape that is flame-retardant and conformable
- Used for protective jacketing and harnessing
- Mechanical protection with minimum bulk
- UL Listed and CSA Certified

[Print](#)

Need Help?

Questions? We can help [Contact Us](#)

Overview

Documents

3M™ Temflex™ Vinyl Electrical Tape is used for protective jacketing and harnessing. Provides excellent mechanical protection with minimum bulk. UL Listed and CSA Certified for 176°F (80°C).

Specifications

Adhesive_Material	Rubber Resin
Agency_Approvals	ASTM D 2301 Type 1, MSHA Approved, CSA, CSA Certified, UL Listed
Backing_Material	Polyvinyl Chloride
Breaking_Strength	17 lb/in
Color	Black
Dielectric_Strength	1000 V/mil
Family	3M™ Temflex™ Vinyl Electrical Tape 1700
Length	66 Linear Foot
Length_metric	20.11 m
Operating_Temperature_Range_Celsius	0 to 80 Degree Celsius
Operating_Temperature_Range_Fahrenheit	32 to 176 Degree Fahrenheit
Product_Family	3M™ Temflex™ Vinyl Electrical Tape 1700
RoHS_2011_65_EU_Compliant	Yes
RoHS_EU_Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls_per_Carton	1
Rolls_per_Case	10
Specifications	MSHA Approved
Tape_Grade	General Use
Tape_Type	Vinyl
Text_on_Tape	MSHA
Thickness	7 mil

Thickness_metric	0.177 mm
Trademark	Temflex
Voltage_Application	Low Voltage
Width	1.5 Inch
Width_metric	38.1 mm