

Catalog Number: TY5232MX
Product ID: 7TAG009010R0010
UPC Number: 78621083937
EAN Number: 05414363065302
Status: Active



Actual



Actual

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 203.2mm (8.0 Inches), Width of 2.54mm (0.10 Inches), Thickness of 1.10mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Pack

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.
- Application Tools: ERG50, WT1-TB

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5037 Cable Ties & Wraps
Brand Name	Ty-Rap
Type	Standard
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Width	0.10 Inch/2.54mm
Length	8.0 Inches/203.2mm
Thickness	0.05 Inch/1.10mm
Bundle Diameter	0.08 Inch/2mm-1.97 Inches/50mm
Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 Pounds/80 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.54mm
Length belt/tape/tie	203.2mm
Tie thickness	1.1mm
Max. bundle diameter	50mm
Min. holding force	80N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Black
Transparent	N

Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	10.5x5x0
Outer Quantity	500
Outer Dimensions (inches)	9.7x4.1x6.3
Weight Uom	1.88 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com