



Powering Business Worldwide

pe.eaton.com

Duplex Receptacle

8300W

UPC:032664705670

Dimensions:

- **Height:** 4.19 IN
- **Length:** 1.3 IN
- **Width:** .88 IN

Warranties: No Data

Specifications:

- **Special Features:** Auto-Grounding
- **Type:** Duplex
- **Allowable Wire Size:** #14 to 10 AWG
- **Amperage Rating:** 20A
- **Mounting Type:** Flush
- **Voltage Rating:** 125V
- **Wiring Method:** Back and side
- **Color:** White
- **Contact Material:** Brass
- **Design Type:** Receptacle
- **Nema Configuration:** 5-20R
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Receptacle Type:** Two-pole, three-wire, grounding
- **Style Type:** Standard
- **Connection Type:** Screw
- **Material:** Nylon face, PVC base

Supporting documents: No Data

Certifications:

- UL
- NOM
- Federal Specification Classification 6233 01

Product compliance: No Data



