



Actual

Catalog Number: UA9FJB
Product ID: 7TAA231050R0004
UPC Number: 03448119672
Status: Active

Schedule 40 Elbow, Size 2 Inches, Bend Radius 36 Inches, Bend Angle 90 Degrees, Material PVC, Belled End

North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5751 Pvc Schedule 40 Elbows
Brand Name	Carlton
Type	Rigid Non-Metallic Conduit-Schedule 40 Elbows
Standard	UL E323335
Material	PVC
Color	Gray
Size	58.58 Inches
Connection	2 Inches
Length	2.375 Inches

European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Plastic
Material quality	PVC
Surface polished	N
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Angle of bow	90°

Packaging

Outer Quantity	1
Outer Dimensions (inches)	39.361x39.063x2.721
Weight Uom	4.06 lbs. Each

Documents / Support Tools

Technical Data Sheet Global	wsd-001725
-----------------------------	------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com