



Item #: **F844-WH**
 Product Family Name: **Light Wave**
 Category: **Interior Fan**
 Certification: **4000048**
 Patents: **U.S. Patent(s): D750,213: Add'l U.S. Patent(s) Pending**
 Notes:

UPC Code: **706411045370**
 Finish: **White**
 Category Type: **Ceiling Fan**



Image File Name:
 F844-WH--
 1398898011.jpg



MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
ABS Construction		Yes	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	3	VARIABLE	14.11
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
4.5	.75	6.0	.75
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
13.75	8.50	80	172x14mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	57		96		139
Amps:	0.23		0.38		0.54
Watts:	11.220		32.330		65.300
CFM:	1752.00		3393.00		5024.00
CFM/Watts:	156.15		104.95		76.94



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
	RCS213	
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
		WCS213

LAMPING

No. of Bulbs:	Light Type:			
1	Led			
Max Bulb Wattage:	Socket:			
17	Led			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
Yes	Yes			
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	3000	80		1100.000

GLASS

Description:	Material:	
	Etched Lens	
Part No.:	Quantity:	
N/A	1	
Width:	Height:	Length:
6.42	1.06	6.42



SHIPPING

Carton Width:	Carton Height:	Carton Length:
14.000	9.630	31.380
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
17.380	2.448	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1

LED



ETL Intertek

LED

Yes

Yes