

Item #: **8763-66-L**
 Product Family Name: **Merrimack™**
 Category: **Wall Mount**
 Certification: **3195126**
 Patents

UPC Code: **747396087122**
 Finish: **Black**
 Category Type: **Wall Bracket**

Notes:



Image File Name:
8763-66-L--
1377129660.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
10		20	12
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	7.91
Canopy Width:	Canopy Height:	Canopy Length:	
6.25	12.00		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		7.25	12.75

LAMPING

No. of Bulbs:	Light Type:			
1	L-Ac10-Module			
Max Bulb Wattage:	Socket:			
10	Led			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
No		30000		Yes
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	2700	78	450.000	220.600



SHIPPING

Carton Width:	Carton Height:	Carton Length:
13.000	23.250	14.500
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
10.208	2.536	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1

SHADE / GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
G8763	1
Width:	Length:

LED



Wet Location



ETL Intertek

Yes

Yes

Yes