



Item #:	<b>F522-ORB</b>	UPC Code:	706411044014
Product Family Name:	<b>Mojo</b>	Finish:	Oil Rubbed Bronze
Category:	<b>Interior Fan</b>	Category Type:	Ceiling Fan
Certification	<b>4000048</b>		
Patents			
Notes:			



Image File Name:  
F522-ORB\_0.jpg



## MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
Plywood Construction		No	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	5	12	17.48
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
3.5	.75	6	.75
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
11.75	9.00	80	153x15mm

  

	Low:	Low/Med:	Medium:	Med/High:	High:
<b>RPM:</b>	85		135		180
<b>Amps:</b>	0.27		0.42		0.55
<b>Watts:</b>	14.100		34.100		65.700
<b>CFM:</b>	2370.00		3750.00		5295.00
<b>CFM/Watts</b>	168.09		109.97		80.59



## FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
Yes	Yes	Yes
	Included Remote Control:	Included Wall Control:
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS213,RCS223	WC106,WCS213,WC S223

## LAMPING

No. of Bulbs:	Light Type:			
3	B10.5 Cand			
Max Bulb Wattage:	Socket:			
60	E12			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
Yes	Yes			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes				

## GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
GF522	1
Width:	Height:
	Length:



## SHIPPING

Carton Width:	Carton Height:	Carton Length:
13.380	11.000	23.000
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
20.570	1.959	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack:
		1



Title 17

Yes



ETL Intertek

Yes