

MINKA-LAVERY®

Item #: 1972-138	UPC Code: 747396044613
Product Family Name: Aspen™ II	Finish: Aspen Bronze™
Category: Wall Sconce	Category Type: Sconce
Certification 3057374	
Patents	
Notes:	



Image File Name:

1972-138--
1377124212.jpg



MEASUREMENTS

Width: 9.25	Length: 12.5	Height: 12.5	Extension: 5.25
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 5.03
Canopy Width: 8.25	Canopy Height: 11.50	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: 6.25	Center to Bottom: 6.38

LAMPING

No. of Bulbs: 1	Light Type: A19,Medium			
Max Bulb Wattage: 100	Socket: E26,Medium			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G5970	Quantity: 1
Width: 7.25	Height: 10.75
	Length:



SHIPPING

Carton Width: 11.500	Carton Height: 9.000	Carton Length: 14.750
Carton Weight: 6.534	Carton Cubic Feet: 0.883	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 1



Damp Location
Yes



Title 17
Yes



ETL Intertek
Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties