



Item #:	UPC Code:
F702-VB	706411009037
Product Family Name:	Finish:
Volterra™	Volterra Bronze™
Category:	Category Type:
Interior Fan	Ceiling Fan
Certification	
E75795	
Patents	
© 2002 Minka Lighting, Inc.	
Notes:	



Image File Name:
F702-VB--
1509648453.jpg



MEASUREMENTS

Blade Finish:				Reversible Blades:
				No
Blade Material:				Slope:
Plywood Construction				No
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:	
52	5	14 degrees	28.24	
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:	
6	0.75			
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:	
15.25	8.50	80	172x20mm	

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	71		106		159
Amps:	0.35		0.47		0.55
Watts:	17.000		34.000		67.000
CFM:	2405.11		3720.42		5424.95
CFM/Watts:	141.48		109.42		80.97



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
		WCS213
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS213	

LAMPING

No. of Bulbs:	Light Type:				
2	T4(E11) Mini Cand Halogen Clear				
Max Bulb Wattage:	Socket:				
50	E11 Mini Cnad				
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight	
Yes	Yes				
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:		Delivered Lumens:
Yes					

GLASS

Description:	Material:				
	Glass				
Part No.:	Quantity:				
GF702	1				
Width:	Height:			Length:	



SHIPPING

Carton Width:	Carton Height:	Carton Length:
15.000	12.380	25.500
Carton Weight:	Carton Cubit Feet:	Small Package Shippable:
31.350	2.740	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1
		Master Pack:
		1



Title 17

Yes



UL Listed

Yes