



31060-782: Three Light Chandelier



Collection: Sussex

Three Light Decorative Chandelier in Heirloom Bronze Finish with Satin Etched Glass Shades.

The look that satisfies discerning taste. Part of our Sussex collection where past elements of design keep pace with today.

Note: Swing arms Function Rotate Arms Up or Down.

UPC #:785652031069

Finish: Heirloom Bronze (782)

Dimensions:

Diameter:	22"	Overall Height:	144"
Height:	15 1/2"	Wire:	144" (color/Brown)
Weight:	7.9 lbs.	Chain:	120"
		Mounting Proc.:	Center Lock-Up
		Connection:	Mounted To Box

Bulbs:

3 - Medium A19 100w Max. 120v - Not included
3 - LED Medium A19 8w Max. 120v - Not included
3 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Adjustable arms rotate for up or down lighting
- A decorative canopy is included
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Material List:

1 Body - Steel - Heirloom Bronze
1 Chain - Steel - Heirloom Bronze

Safety Listing:

Safety Listed for Dry Locations
Safety Listed for Dry Locations

Instruction Sheets:

English (HC-678)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	3				4 1/16	7 1/2	1 11/16			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3			6 3/4		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	-----------	----------

Individual	31060-782	1	785652031069	18	15.25	8.25	1.311	10	125	Yes
NJ Pallet		44		48	40	75.5	83.889	440		No
NV Pallet		44		48	40	75.5	83.889	440		No