

Item #: **P4086-1-084**  
 Product Family Name:  
 Category: **Low Voltage Track**  
 Certification: **E254993CCC**  
 Patents  
 Notes:

UPC Code: **874944007988**  
 Finish: **Brushed Nickel**  
 Category Type: **LightRail**



Image File Name:  
 P4086-1-084--  
 1509668792.jpg



## MEASUREMENTS

Width:	Length:	Height:	Extension:
	<b>120</b>	<b>11</b>	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
<b>No</b>			<b>No</b>
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight:
<b>8</b>		<b>No</b>	<b>8.29</b>
Canopy Width:	Canopy Height:	Canopy Length:	
<b>5.75</b>	<b>5.25</b>		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

## LAMPING

No. of Bulbs:	Light Type:			
<b>6</b>	<b>Mr-16 (Gu5.3,12v)</b>			
Max Bulb Wattage:	Socket:			
<b>35</b>	<b>Gy6/Gu5/3g4,2-Pin</b>			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
<b>No</b>				<b>Yes</b>
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
<b>Yes</b>				



## SHIPPING

Carton Width:	Carton Height:	Carton Length:
<b>6.000</b>	<b>10.000</b>	<b>41.250</b>
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
<b>11.770</b>	<b>1.432</b>	<b>Yes</b>
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		<b>1</b>
		Master Pack:
		<b>1</b>

## SHADE / GLASS

Description:	Material:
	<b>Glass</b>
Part No.:	Quantity:
<b>GKSH2100</b>	<b>6</b>
Width:	Height:
<b>3.25</b>	<b>2.25</b>
	Length:



Title 17

Yes



UL Listed

Yes