

Item #: 8766-66-L	UPC Code: 747396087146
Product Family Name: Merrimack™	Finish: Black
Category: Post Mount Lantern	Category Type: Post Light
Certification 3195126	
Patents	
Notes:	



Image File Name:
8766-66-L--
1377129660.jpg



MEASUREMENTS

Width: 8	Length: 19.25	Height: 19.25	Extension: No
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 4.63
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 1	Light Type: L-Ac10-Module			
Max Bulb Wattage: 10	Socket: Led			
Dimmable: No	Ballast:	Rated Life Hours: 30000	Photocell included:	Lamps included: Yes
LED Included: Yes	Color Temp.: 2700	CRI: 80	Initial Lumens: 450.000	Delivered Lumens: 189.180



SHIPPING

Carton Width: 10.000	Carton Height: 17.000	Carton Length: 10.000	
Carton Weight: 6.248	Carton Cubit Feet: 0.984	Small Package Shippable: Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack: 1

SHADE / GLASS

Description:	Material: Glass	
Part No.: G8762	Quantity: 1	
Width:	Height:	Length:

LED

LED

Yes



Wet Location

Yes



ETL Intertek

Yes