

Item #: P961-077	UPC Code: 844349009160
Product Family Name: Grid™ II	Finish: CHROME
Category: Mini-Pendants	Category Type: Pendant
Certification 3057374	
Patents	
Notes: Adjustable to 17"H min. 53"H max.	



Image File Name:
P961-077--
1377188249.jpg



MEASUREMENTS

Width: 5.75	Length: 5.75	Height: 20	Extension:
Height Adjustable: Yes	Min Overall Height: 56.00	Max Overall Height: 44.00	Slope: Yes
Wire Length: 72"	Chain Length:	Safety Cable Included: No	Net Weight: 4.06
Canopy Width: 5.00	Canopy Height: 1.00	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 1	Light Type: T-10,Med			
Max Bulb Wattage: 60	Socket: E26,Med			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: P961	Quantity: 1
Width: 4.75	Height: 10.00
	Length:



SHIPPING

Carton Width: 6.880	Carton Height: 16.750	Carton Length: 6.880
Carton Weight: 4.710	Carton Cubit Feet: 0.459	Small Package Shippable: Yes
Master Pack Width: 14.380	Master Pack Height: 17.380	Master Pack Length: 21.500
Master Pack Weight: 29.480	Master Cubic Feet:	Multi-Pack: 6



Title 17

Yes



ETL Intertek

Yes