



## Weatherproof Outlet Covers : Plastic & Extra-Duty Plastic

### WP3100C | Plastic In-Use Weatherproof Cover - Single-Gang



#### WP3100C

#### PLASTIC IN-USE WEATHERPROOF COVER - SINGLE-GANG

Plastic In-Use Weatherproof Covers are easy to install and include adhered gasket, mounting screws, base, cover assembly, and inserts to meet the needs of a variety of applications.



#### Features & Applications

##### Features

- Complies with 2014 NEC Article 314.15 for damp and wet locations
- Exceeds CEC Article 26-702
- UL Certified for Type 3R outdoor enclosures
- Meets requirements for cold impact testing: -60° F (-51° C)
- Heavy-duty UV stabilized polycarbonate cover, mounting base and inserts
- 1/8" (3 mm) thick, pre-adhered neoprene gasket with slits for mounting screws
- Lockable hasp: All models accept up to 1/4" (6 mm) dia shank
- Except WP3100C & WP3103C accept up to 1/8" (3 mm) dia shank
- Three inserts provided with all models that allow each model to meet multiple installations (up to 16 configurations)
- Max cord size: (2) #14 AWG or (1) #12 AWG
- Mounts vertically or horizontally
- Warranty: 1-year limited

##### Applications

- Industrial
- Commercial
- Manufacturing
- Residential
- Agricultural
- Signage
- Athletic Fields

Specifications

Gang Type

Single

Color

Clear

Is Extra Duty Rated

No

Hinge Direction

Vertical, Horizontal

Insert Types Included

WP17

Number of Included Inserts

3

Weatherproof Cover Material

UV Stabilized Plastic

Product Height (mm)

146.6

Product Width (mm)

103.1

Product Depth (mm)

70

Warranty

1-year limited

Resources & Support



NewsRoom

Get News, Product Info, Applications, Energy Savings and More...



Catalogs

Flip Through Our Products



Support

Easily Find Contact Information