

2677H

Housing Pack for 2678F, 2679F, 2680F, FL2679F, FL2679FT, FL2680F and FL2680FT. Type IC. Mounting ears.

★★★★★

Write the first review

Product Q&A

Be the first to ask a question.

- Download catalog
- Shop for Parts
- Share
- Print



Overview	Specifications	Accessories	Where To Buy	Reviews	Answers
----------	----------------	-------------	--------------	---------	---------

Baths up to () Sq Ft	N/A
Ceiling Installation	Yes
CFM @ 0.10"	Housing Pack Only
CFM @ 0.125"	N/A
CFM @ 0.25"	N/A
Color	N/A
CSA	No
cUL Listed	No
Duct Direction	Horizontal
Duct Size	4"
ENERGY STAR® qualified	No
Globe Glass Color	N/A
Grille Finish	N/A
Grille Length	N/A
Grille Width	N/A
Heater wattage	N/A
Housing Dimensions L x W x H	8" x 8-1/4" x 5-3/4"
Housing Height	5-3/4"
Housing Length	8"
Housing Width	8-1/4"
Humidity Sensing	No
HVI Certified	No
Light Bulb Quantity	0
Light Bulb Wattage	100
Light Bulbs Included	No
Lighting Type	No Light
Material	N/A
Minimum construction space required	2x6
Motor engineered for continuous operation	No
Nightlight	No
Product Weight	10.0 lbs
Project Pack	Yes
Rated Amps	N/A
Rated Sones - Vertical	N/A
Rated Watts	N/A
Sones	N/A
UL Listed for use over bathtubs or showers when connected to a GFCI circuit	Yes
Wall Installation	No
Warranty	1 Year
Watts @ 0.1"	N/A

