

# MINKA-LAVERY®

|                      |                          |
|----------------------|--------------------------|
| Item #:              | UPC Code:                |
| <b>4848-276</b>      | <b>747396091686</b>      |
| Product Family Name: | Finish:                  |
| <b>Lucero</b>        | <b>Florentine Silver</b> |
| Category:            | Category Type:           |
| <b>Chandeliers</b>   | <b>Chandelier</b>        |
| Certification        |                          |
| <b>4009158</b>       |                          |
| Patents              |                          |
| Notes:               |                          |



Image File Name:  
4848-276--  
1398894164.jpg



## MEASUREMENTS

|                    |                     |                        |                   |
|--------------------|---------------------|------------------------|-------------------|
| Width:             | Length:             | Height:                | Extension:        |
| <b>24</b>          | <b>24</b>           | <b>28.5</b>            |                   |
| Height Adjustable: | Min Overall Height: | Max Overall Height:    | Slope:            |
| <b>Yes</b>         | <b>32.63</b>        | <b>106.13</b>          | <b>Yes</b>        |
| Wire Length:       | Chain Length:       | Safety Cable Included: | Net Weight        |
| <b>120</b>         | <b>72</b>           | <b>No</b>              | <b>15.43</b>      |
| Canopy Width:      | Canopy Height:      | Canopy Length:         |                   |
| <b>5.13</b>        | <b>1.00</b>         | <b>5.13</b>            |                   |
| Backplate Width:   | Backplate Height:   | Center to Top:         | Center to Bottom: |

## LAMPING

|                   |                         |                   |                     |                   |
|-------------------|-------------------------|-------------------|---------------------|-------------------|
| No. of Bulbs:     | Light Type:             |                   |                     |                   |
| <b>9</b>          | <b>B10.5,Candelabra</b> |                   |                     |                   |
| Max Bulb Wattage: | Socket:                 |                   |                     |                   |
| <b>60</b>         | <b>E12,Candelabra</b>   |                   |                     |                   |
| Dimmable:         | Ballast:                | Rated Life Hours: | Photocell Included: | Lamps Included:   |
| <b>Yes</b>        |                         |                   | <b>N</b>            | <b>No</b>         |
| Lamp Included:    | Color Temp.:            | CRI:              | Initial Lumens:     | Delivered Lumens: |
| <b>No</b>         |                         |                   |                     |                   |



## SHIPPING

|                     |                     |                          |
|---------------------|---------------------|--------------------------|
| Carton Width:       | Carton Height:      | Carton Length:           |
| <b>26.750</b>       | <b>11.250</b>       | <b>26.750</b>            |
| Carton Weight:      | Carton Cubic Feet:  | Small Package Shippable: |
| <b>22.572</b>       | <b>4.659</b>        | <b>Yes</b>               |
| Master Pack Width:  | Master Pack Height: | Master Pack Length:      |
|                     |                     |                          |
| Master Pack Weight: | Master Cubic Feet:  | Multi-Pack:              |
|                     |                     | <b>1</b>                 |

## SHADE / GLASS

|              |           |
|--------------|-----------|
| Description: | Material: |
| Part No.:    | Quantity: |
| Width:       | Height:   |
|              | Length:   |



ETL Intertek

Yes