



Measurements:

<u>Height</u>	<u>Width</u>
5.00"	9.00"
<u>Hanging Weight</u>	

Lamping:

Incandescent MB Incandescent	1,344 Rated Lumens
2.00 60W MB Incandescent	Color Temperature
120 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
1.31 lb	11.29"	6.29"	11.29"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
23.15 lb	12.01"	26.77"	23.43"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
8.0000	783209588509	Yes	

Finish:

Satin Nickel SN

Glass:

Marble MR

Material:

Steel

Certification:

Dry Location  
Location

Additional:

MB Incandescent (Not Included)