



*height from center of outlet to the top of the fixture

Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
26.50"	12.50"	12.00"
<u>BP Height</u>	<u>BP Width</u>	<u>HCO</u>
15.50"	6.50"	12.00000"
<u>Hanging Weight</u>		
11.68 lb		

Lamping:

Incandescent CA Incandescent	2,016 Rated Lumens
3.00 40W CA Incandescent	Color Temperature
120 total watt	1,500 Rated Life
Dimmable : Standard Dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
14.60 lb	17.13"	14.37"	28.35"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209349704	Yes	

Finish:

Oriental Bronze OB

Glass:

Water Glass WG

Material:

Die Cast Aluminum

Certification:

Wet Location
 Location

Additional:

CA Incandescent (Not Included)