



Powering Business Worldwide

pe.eaton.com

Definite Purpose Control - Starter

A25SNC25A

UPC:782113757896

Dimensions:

- **Height:** 7.14 IN
- **Length:** 3.69 IN
- **Width:** 2.5 IN

Weight:1.8 LB

Warranties:

- 1 year

Specifications:

- **Model:** Starter
- **Amperage Rating:** 25A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Control Characteristics:** Separate control wiring
- **Enclosure:** Open with metal mounting plate
- **Phase:** Three-phase
- **Terminals:** Screw/pressure plate
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [A25_NC 2D Drawing Xchange](#)
- [Eaton Specification Sheet - A25SNC25A](#)
- [A25_NC 3D Model Xchange](#)
- [A25_NC 2D PDF](#)
- [A25_NC 3D Inventor](#)
- [A25_NC AutoCAD 2D Footprint \(mm\)](#)
- [A25_NC AutoCAD 2D Footprint](#)

Certifications:

- CSA Certified
- UL Recognized



Product compliance: No Data

© 2016 Eaton. All rights reserved.