



Powering Business Worldwide

pe.eaton.com

Definite Purpose Control - Contactor

C25ENF440B

UPC: 782113536606

Dimensions: 3.38 IN * 2.68 IN * 3.75 IN (L * W * H)

Notes: Resistive Load rating per pole

Warranty: 1 year

Specifications:

- **Connection:** Quick
- **Amperage Rating:** 40A
- **Coil:** 208-240 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 25-40A, four-pole
- **Model:** Contactor
- **Number Of Poles:** Four-pole
- **Resistive Load:** 50A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25ENF4 3D Model Xchange](#)
- [C25ENF4 2D PDF](#)
- [C25ENF4 2D Drawing Xchange](#)
- [C25ENF4 AutoCAD 2D Footprint](#)
- [C25ENF4 AutoCAD 2D Footprint \(mm\)](#)
- [C25ENF4 3D Inventor](#)
- [Eaton Specification Sheet - C25ENF440B](#)

Certifications: No Data

Product compliance: No Data

