



Brand: Craftmade

SKU: MI52AGVM

Name: 52" Ceiling Fan with Blades Sold Separately

Finish: Aged Bronze Vintage Madera

Collection: Mia

UPC: 647881052720

PRODUCT DETAILS

Product ID: 167981
Light Source: CFL
Shown With: B552S-MIA (sold separately)
Glass: Tea-Stained
Style: Traditional
Wire: 80
Weight: 23.32lbs.
Bulbs: 2
Bulb Base: Medium
Max Watts: 13
Bulbs Included: Yes
Blades Included: No
Blades: 5
Sweep: 52
Blade Pitch: 14°
Blades: Type 1, Type 2
Light Kit Included: Yes
Motor Size: 188 x 15
Ceiling Fan Amps at High Speed: 0.7
Watts (high): 67

RPM: 210-120-78
Airflow: 5432
Efficiency: 81
Downrod: 2"
Downrod: 6
Motor Only: Yes
Light Kit: Formed Bowl Light Kit (2-13W CFL Bulbs Included)
Remote Info: MI-ICS-AGVM sold separately
Voltage: 120v
Remote Options: Intelligent control offering 65,000 different frequency settings
Warranty: Lifetime Limited
Fan Size: Small, Medium
Motor Type: AC
Listing: ULus
Location: Indoor
Mounting: Dual Mount
Shipping: L:25.04"

ADDITIONAL PRODUCT INFORMATION

- AGVM Finish uses AG (Aged Bronze) Accessories and AWD Finish uses AW (Antique White) Accessories

MI52AGVM - Craftmade

Craftmade Brands is proud to present this aged bronze vintage madera finished ceiling fan, by Craftmade. The MI52AGVM is made from premium materials, this Ceiling Fan offers great function and value for your home. This fixture is part of Craftmade's decorative Mia Collection, so make sure to check out other traditional fixtures to accessorize your room.

For more than 30 years, Craftmade has earned lighting showrooms' loyalty with great designs, top product quality and service that puts customers first. Some vendors promise more than they deliver; here at Craftmade, we deliver what we promise, with same day/next day shipping on more than 5,000 in-stock items. And there are more reasons to buy and sell Craftmade products: Efficiency. Consistency. Delivering what you need, when you need it. Choose Craftmade Brands for a dependable partnership—and quality fans and lighting for every part of your home.