



## Lampholders, Garden Lights & Accessories

**T&B Catalog Number:**

DL-80-WH

**UPC Number:**

04226981032

**Status:**

Obsolete

**Description:**

Lampholder, 1 Lamp, White, Die Cast Zinc, 150 Watt Maximum Par 38 or R40 Lamp, Includes Inside Gasket and Ground Screw

### Features

Clean lines and precision manufacturing result in a fixture which will enhance any application.

High quality replaceable porcelain socket with high-temperature leads allow for easy field maintenance.

Positive locking mounting arm keeps fixture in aimed position to reduce costly call-backs and ground screw boss in arm.

### Application

Low maintenance indoor/outdoor lighting where moisture, dirt, dust, corrosion and rough service are problems.

To light cold storage facilities, walkways, bridges, tunnels and security locations.

Used with colored globes as warning, caution or directional lights.

### General

T&B Replacement Catalog Number S500WHE-RL

Material Die Cast Zinc

Color White

Maximum Wattage 150

### Packaging

Package in Units 24

T&B Sold in UOM Each

T&B Weight Per UOM 0.38 lbs. Each

### Application Support

Product Overview Available on Website

Product Brochure-Universal Flip-Lid Cover Available on Website

Product Brochure-Weatherproof While-in-Use Kits Available on Website

D-Pak Merchandising System Available on Website

Industry Cross Reference Available on Website

### Notes

Suitable for use in wet locations.

### Certifications



File Nbr:

E 51152

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)