

MINKA-LAVERY®

Item #: **4107-172**
 Product Family Name:
 Category: **Semi Flush**
 Certification: **4000164**
 Patents
 Notes:

UPC Code: **747396091259**
 Finish: **Smoked Iron**
 Category Type:



Image File Name:
 4107-172--
 1398894164.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
15	15	10	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	3.37
Canopy Width:	Canopy Height:	Canopy Length:	
6.00	0.75		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs:	Light Type:			
3	A-19,Med			
Max Bulb Wattage:	Socket:			
60	E26,Med			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes			N	No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Carton Width:	Carton Height:	Carton Length:
16.000	9.000	16.000
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
5.676	1.333	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1

SHADE / GLASS

Description:	Material:
	Fabric
Part No.:	Quantity:
SH4107	1
Width:	Height:
15.00	4.50
	Length:
	15.00



ETL Intertek

Yes