

GENERATION LIGHTING

84032-746: One Light Outdoor Wall Lantern



Dimensions:

Width:	8 1/2"	Extends:	9 1/2"
Height:	19 1/4"	Wire:	6 1/2" (color/Black/White)
Weight:	5.7 lbs.	Mounting Proc.:	Cap Nuts
		Connection:	Mounted To Box
		Bulb Appearance:	Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Fixture may be mounted in the up or down position
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Collection: Kent

One Light Outdoor Wall Lantern in Oxford Bronze Finish with Clear Seeded Glass.

Outdoor wall lantern finished in Oxford Bronze over die-cast aluminum with clear seeded glass.

Design #: D20034

UPC #:785652999802

Finish: Oxford Bronze (746)

Material List:

1 Body - Die Cast Aluminum - Oxford Bronze

Safety Listing:

Safety Listed for Wet Locations
Safety Listed for Wet Locations

Instruction Sheets:

English (HC-407)
French (F-009)
Trilingual (English, Spanish, and French)
(990W84030-84530-84032-84532-KEN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Seeded	4									
Panel	Glass	Clear Seeded	4									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			5/8	5 1/2	16 1/2	2 3/4

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	84032-746	1	785652999802	21.75	11.25	10.25	1.451	5.9	175	Yes
NJ Pallet		42		48	40	73.5	81.667	247		No
NV Pallet		56		48	40	72	80	399		No