



7569-15: Two Light Outdoor Ceiling Flush Mount



Collection: Outdoor Ceiling

Close to Ceiling Outdoor Decor Fixture in White Polypropylene with Clear Textured Glass. U.L. Listed for Damp Location.

White Outdoor Light with Clear Textured Glass Panels. Polypropylene construction offers non-corrosive, rust-free, outdoor solution.

UPC #:785652756955

Finish: White (15)

Dimensions:

Length:	10 1/4"	Wire:	6 1/2"
Width:	10 1/4"	Connection:	Mounted To Box
Height:	5 1/2"	Bulb Appearance:	Clear
Weight:	2.9 lbs.		

Bulbs:

2 - Medium A19 60w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Polypropylene - White

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

English (HC-332)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Textured	4									

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frts. Class	UPS Ship
Individual	7569-15	1	785652756955	10.5	10.5	6	0.383	3.6	100	Yes
Master Pack		6	10785652756952	32	11.18	13	2.691	22.9	100	Yes
NJ Pallet		150		48	40	70	77.778	572.5		No
NV Pallet		150		48	40	70	77.778	572.5		No