G25 Timeless, Vintage Inspired Lamp

Item Number 04127

Specifications

Energy Used (Watts)	. 60
Domestic Code	. VINTAGE/60/G25
Volts	. 120
Brightness (Lumens)	. N/A
Average Rated Hours	. 1500
Life (in years)*	. 1.3
Dimmable	. Yes
Filament Type	. 32-Anchor
Estimated Yearly Energy Cost**	. \$7.23
Package Type	. Card, Tray Pack
Country of Origin	. China



Finish	Clear
Base	E26 (Medium)
MOL	4.53"



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

(W),WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

^{*}Based on 3 hrs./day

^{**} Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.