



# S3142

150T3Q/CL/L/118MM

150 watt; Halogen; T3; Clear; 1500 Average rated Hours; 2400 Lumens; Double Ended base; 118mm; 120 volts



## Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output

S3142

| Item Number | UPC          | Watts | Voltage | Lamp Shape | Base         | ANSI Base | Lamp Code         |
|-------------|--------------|-------|---------|------------|--------------|-----------|-------------------|
| S3142       | 045923031427 | 150   | 120     | T3         | Double Ended | R7s       | 150T3Q/CL/L/118MM |

| Finish | MOL In Inches | MOD In Inches | Filament | Initial Lumens | Kelvin Temp | Color      | Average Rated Hours |
|--------|---------------|---------------|----------|----------------|-------------|------------|---------------------|
| Clear  | 4-11/16"      | 0.38"         | C-8      | 2400           | 2900        | Warm White | 1500                |

| Pack   | Package Type | Dimmable/Non-Dimmable | RoHS Compliant |
|--------|--------------|-----------------------|----------------|
| 480/12 | Box          | Dimmable              | Yes            |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

