



S3934

75A21/IF
75 watt A21 Incandescent; Frost; 5000 average rated hours;
680 lumens; Medium base; 130 volts

Features

- General Service Incandescent
- Household or Commercial use
- Long Life
- 130 volt



S3934

Item Number		UPC		Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3934		045923039348		75	A21	Medium	E26	75A21/IF	130
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type		
Frost	5-5/16"	2.63"	C-9	680	5000	120/6	Sleeve		
Dimmable/Non-Dimmable				CEC Status			RoHS Compliant		
Dimmable				Non-Compliant			Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

