



Dependable Power for Any Application

hubbell-acmeelectric.com

www.hubbell.com

120/208/240/277 - 120/240
120/208/240/277 Primary Volts - 120/240 Secondary Volts - 1Ø
Dry Type Distribution Transformer - Single Phase

1001



Catalog #: T279747S

PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeelectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	15.00
Primary Voltage:	120/208/240/277
Secondary Voltage:	120/240
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	16.94 (43.0)
Width (In./cm):	14.12 (35.9)
Depth (In./cm):	11.59 (29.4)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	1.00-1.50 (2.5-3.8)
Wiring Diagram:	63

PACKAGING

Ship Weight (Lbs/Kg): 171 (77.6)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf