



S3467

35MR11/NFL
35 watt; Halogen; MR11; FTH; 2000 Average rated Hours; Sub
Minature 2 Pin base; 12 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output
- 12 volt



S3467

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S3467	045923034671	35	12	MR11	Sub Minature 2 Pin	GZ4	35MR11/NFL
ANSI Code	MOL In Inches	MOD In Inches	Filament	Kelvin Temp	Color	Average Rated Hours	Pack
FTH	1-1/4"	1-3/8"	C-6	2900	Warm White	2000	120/12
Package Type	Beam Spread Deg	CBCP	Dimmable/Non-Dimmable		CEC Status	RoHS Compliant	
CD/1	24	800	Dimmable		Non-Compliant	Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

